



Sign in



Resister

Japanese

English

Product Category

Environment

About SATO PARTS

Contact us

My list

SATO PARTS CO.,LTD. > Product Category > Binding.post / Tip Plug & Jack

Product mass

Precautions for use

General notes

T-12-12

made in JAPAN



Order model number

- Order model numberT-12-12-[Body color]
- Order exampleT-12-12-R (An example of an order with a red color.)

Basic information

Dimension

Soldering heat resistance conditions

Download

Download

Add to My List



Sample request (Only available in Japan)

Attention: This download system is supported by Google Chrome, Microsoft Edge and Mozilla Firefox.

Please read the [download terms](#) when downloading data.

*For the Environmentally Friendly Substances Report, please see [our Environmental Initiatives](#).
*For tools to view chemSHERPA data, see the [download procedure](#) **PDF**. For the [survey list](#) **PDF**, please see here.
* If red phosphorus is intentionally added, it is voluntarily reported by chemSHERPA.

For the versions of chemSHERPA data, Conflict Minerals Reporting Template (CMRT) and Extended Minerals Reporting Template (EMRT) that are supported by our products, please see [the version correspondence table](#) .

Please select the file to download.Items that cannot be checked can only be downloaded by signed-in members. Please sign in and select.



T-12-12[Common files]

- ☐ Specification
- ☐ Product test report
- ☐ 2D CAD data (dxf)
- ☐ 3D CAD data (ipt)
- ☐ 3D CAD data (stp)
- ☐ 3D CAD data (x_b)
- ☐ 3D PDF
- ☐ Certificate of non-applicability of US EAR
- ☐ Parameter Sheet



T-12-12-B

- ☐ chemSHERPA data
- ☐ Report on RoHS Directive
- ☐ CMRT
- ☐ EMRT (xlsx)
- ☐ Country of origin (pdf)



T-12-12-R

- ☐ chemSHERPA data
- ☐ Report on RoHS Directive
- ☐ CMRT
- ☐ EMRT (xlsx)
- ☐ Country of origin (pdf)

Home

Product search

Product Category

About SATO PARTS

News classification

Contact us

Video channel

Download brochure

Environmental initiatives

Privacy policy

Cookie policy

Download terms

Terms of Use