







PC board drilling dimensions(after plating)
(thickness $\leq 3.20 \pm 0.30 \text{mm}$)



	±0.38	±0.12	±0.10	±0.25	±0.07	PART NUMBER	PART NUMBER	PART NUMBER
SHELL								
09	30.81	24.99	16.96	16.79	10.96	D09P90C4P00	D09P90C6P00	D09P90C8P00
15	39.14	33.32	25.18	25.12	19.18	D15P90C4P00	D15P90C6P00	D15P90C8P00
25	53.03	47.04	39.12	38.84	33.12	D25P90C4P00	D25P90C6P00	D25P90C8P00
37	69.32	63.50	55.68	55.30	49.68	D37P90C4P00	D37P90C6P00	D37P90C8P00
						gold flash	0.76» gold	1.25» gold

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P90C4P.V00LF	D09P90C6P.V00LF	D09P90C8P.V00LF
15	39.14	33.32	25.18	25.12	19.18	D15P90C4P.V00LF	D15P90C6P.V00LF	D15P90C8P.V00LF
25	53.03	47.04	39.12	38.84	33.12	D25P90C4P.V00LF	D25P90C6P.V00LF	D25P90C8P.V00LF
37	69.32	63.50	55.68	55.30	49.68	D37P90C4P.V00LF	D37P90C6P.V00LF	D37P90C8P.V00LF

gold flash	0.76» gold	1.25» gold
------------	------------	------------

rev	econ no	dr	date
B	-	MAS	2000/07/27
C	LS05-004	MPE	2005/02/07
D	LS06-0095	LGO	2006/06/19
E	LS06-0140	LGO	2006/09/22
F	109-0268	NG	2009-11-24
-	-	-	-
-	-	-	-

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:									
SEE DRAWING C01-8646-0001									
European Views									
www.fciconnect.com		surface		tolerance std		projection		mm	
		ISO 1302		ISO 406 ISO 1101					
		TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	MASSON	2000-07-27	ANGULAR	0.X		±0.1	size	Scale	
Eng	PESSON	2000-07-27	LINEAR	0.XX		±0.1	A3	2	
Chr	NIRMAL	2009-11-24	0.XX ±2	0.XXX		±0.1	ECN	109-0268	
Appr	NIRMAL	2009-11-24	Product family			D-SUB	Spec ref -		
		MALE CONNECTOR DELTA D LOW PROFIL				Rev.			
		straight press-fit				F			
title		MALE CONNECTOR DELTA D LOW PROFIL				dwg no		C01-8646-0035	
catalog no		-				CUSTOMER		sheet 1 of 1	