**Part Number :** 526102033
**Product Description :** Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 20 Circuits, Tin-Silver-Bismuth Plating
**Series Number :** 52610
**Status :** Obsolete
**Product Category :** FFC / FPC Connectors



Obsolete

## Documents and Resources

Symbol and Footprint (Multi-Format)

**Specifications**

PS-52610-032-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Obsolete |
| Category | FFC / FPC Connectors |
| Series | Slider |
| Description | Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 20 Circuits, Tin-Silver-Bismuth Plating |
| Product Name | Easy-On |
| UPC | 887191316215 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 125V |

### Physical

| | |
|---|---|
| Actuator Type | Slider |
| Circuits (Loaded) | 20 |
| Color - Resin | Natural |
| Contact Position | N/A |
| Durability (mating cycles max) | 30 |
| Flammability | 94V-0 |
| Mated Height | 5.75mm |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin-Silver-Bismuth |

Obsolete

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Plating Termination | Tin-Silver-Bismuth |
| Material - Resin | Nylon |
| Net Weight | 931.500/mg |
| Orientation | Vertical |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Mounting | Surface Mount |
| PCB Retention | No |
| PC Tail Length | 2.00mm |
| Pitch - Mating Interface | 1.00mm |
| Pitch - Termination Interface | 1.00mm |
| Polarized to PCB | No |
| Stackable | No |
| Temperature Range - Operating | -40° to +85°C |
| Wire/Cable Type | FFC/FPC |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 1.00mm Pitch Premo-Flex FFC Jumpers | 15167 |
| 1.00mm Pitch Premo-Flex FFC Jumpers | 15267 |
| 1.00mm Pitch Premo-Flex FFC Jumpers | 98267 |

Obsolete



Downloaded from Arrow.com.