

Downloaded from Arrow.com.



FTH–13S–01



FTH–13R–01

NOTES:
1. MATERIAL: NYLON 6/6 (RMS–01),
   COLOR NATURAL.

2. FLAME RETARDANT NYLON (RMS–19).
   COLOR NATURAL.
   AVAILABLE BY SPECIAL ORDER ONLY;
   TO ORDER USE P/N FTH–13R–19 OR FTH–13S–19.

3. UV STABILIZED NYLON 6/6 (RMS–46),
   COLOR BLACK.
   AVAILABLE BY SPECIAL ORDER ONLY;
   TO ORDER USE P/N FTH–13R–UVB OR FTH–13S–UVB.

4. MOUNTING SCREW FOR FTH–13R: NO. 8 (M4) PAN HEAD,
   MOUNTING SCREW FOR FTH–13S: NO. 8 (M4) FLAT HEAD OR
   NO. 6 (M3.5) FLAT, ROUND, OR PAN HEAD.
5. PACKAGING QUANTITIES ARE REFLECTED AS THE SUFFIX "–LETTER".
   EXAMPLE: FTH–13S–01–M FOR 1000 PCS.
   –C = 100 PCS
   –M = 1000 PCS

MOUNTING RIVETS FOR – FTH–13R		
USE RIVET NO.	HOLE DIA.	FOR PANEL THICKNESS RANGE
SR–4050	.161 (4.1)	.018–.058 (0.5–1.5)
SR–4060		.058–.097 (1.5–2.5)
SR–4070		.097–.137 (2.5–3.5)
SR–4080		.137–.176 (3.5–4.5)
SR–4100		.215–.255 (5.5–6.5)

REV	DESCRIPTION	ENGR DATE
F	ADDED NOTE 5. SEE CO 200661	SK 05.12.11
E	SEE CO 200570 FOR CHANGES	SK 08.04.10
D	SEE ECN #1124 FOR CHANGES	SK 01.24.06
C	UPDATED PRINT AND CHANGED FILE NO.	SM 05.20.02
B	REDRAWN TO INCLUDE FTH–13S–01 DWG.	RG11/02/00
A	FR NYLON 66 (RMS–19) ADDED	JL 01.06.00

TITLE: FLAT TIE HOLDER

DWG IN IN (MM)

TOLERANCES UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE # FTH–13X
MAT'L: SEE NOTES
RE: RICHCO, INC.

DWN: E.P. APP:
DT: 12–30–98 DT:

RICHCO INC.
PO BOX 804238,CHICAGO,60680
(773) 539–4060

FINAL

PART # FTH–13 SERIES

PRINT TYPE CA