



Part Number : [2070190012](#)
Product Description : Mini-Fit Sigma Sealed Cap for 12 Circuit Plug Housing
Series Number : 207019
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[Drawing 2070190012_sd.pdf](#)
[Packaging Design Drawing 2070180000-PK-000.pdf](#)

3D Models and Design Files

[3D Model 2070190012_stp.zip](#)

Specifications

[Application Specification 2070170000-AS-000.pdf](#)
[Product Specification 2070170000-PS-000.pdf](#)
[Test Summary 2070170001-TS-000.pdf](#)
[Test Summary 2070170000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Accessories
Series	207019
Description	Mini-Fit Sigma Sealed Cap for 12 Circuit Plug Housing
Component Type	Cap
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma Sealed
UPC	193264428595

Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Thermoplastic Elastomer
Net Weight	8.346/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Use with Part(s)

Description	Part Number
Mini-Fit Sigma Sealed Plug Housing, Dual Row, 4.20mm Pitch, 12 Circuits, UL94V-0, Natural	<u>2070170012</u>

This document was generated on Sep 26, 2024