

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2021
© COPYRIGHT 2021 BY - ALL RIGHTS RESERVED.


| REVISIONS | | | | | |
|---|---|---|---|---|---|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | 1 | PRELIMINARY RELEASE | 30JUL2021 | SS | VS |





SECTION A-A




1x2 POSITION



1x3 POSITION




SCALE 3:1





1x4 POSITION


1. MATERIAL: PBT, GLASS FILLED WITH RUBBER GANG SEAL PRE-INSTALLED. GANG SEAL WIRE INSULATION RANGE IS 2.45 TO 3.60 MM.
   KEY A: NATURAL; KEY B: GREY; KEY C: BROWN
   KEY D: RED; KEY E: ORANGE; KEY F: VIOLET
   KEY G: YELLOW; KEY H: BLUE; KEY I: GREEN
2. MATERIAL MARK: PBT GF
3. APPLICABLE CONTACT P/N:
   2329907-*/2329908-*/2329911-*
4. MATING CONNECTOR P/N
   MATES WITH: *-2391576-*, *-2378159-*
   BACK COVER: 2334614-*
   GANG SEAL: 2325349-*, SEE CHART BELOW
5. RECOMMENDED PANEL THICKNESS: 0.80-2.00
6. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
7. FLAMMABILITY RATING: UL94 V-0
8. PRELIMINARY PARTS, NOT RELEASED FOR PRODUCTION


THIS PRODUCT HAS NOT COMPLETED QUALIFICATION TESTING




































THIS PRINT IS
# PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT




RECOMMENDED PANEL CUT-OUT
(ALL DIMENSIONS ±0.15)

| | | | | | | | |
|---|---|---|---|---|---|---|---|
| BLUE | 2325349-4 | 22.85 | 30.73 | 22.52 | KEY C | 1*4 | 3-2391577-4 |
| BLUE | 2325349-4 | 22.85 | 30.73 | 22.52 | KEY B | 1*4 | 2-2391577-4 |
| BLUE | 2325349-4 | 22.85 | 30.73 | 22.52 | KEY A | 1*4 | 1-2391577-4 |
| BLUE | 2325349-3 | 17.85 | 25.73 | 17.52 | KEY C | 1*3 | 3-2391577-3 |
| BLUE | 2325349-3 | 17.85 | 25.73 | 17.52 | KEY B | 1*3 | 2-2391577-3 |
| BLUE | 2325349-3 | 17.85 | 25.73 | 17.52 | KEY A | 1*3 | 1-2391577-3 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY I | 1*2 | 9-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY H | 1*2 | 8-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY G | 1*2 | 7-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY F | 1*2 | 6-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY E | 1*2 | 5-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY D | 1*2 | 4-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY C | 1*2 | 3-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY B | 1*2 | 2-2391577-2 |
| BLUE | 2325349-2 | 12.85 | 20.73 | 12.52 | KEY A | 1*2 | 1-2391577-2 |
| SEAL COLOR | SEAL P/N | DIM C | DIM B | DIM A | KEYING | POSITIONS | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.2
2 PLC ±0.10
3 PLC ±-
4 PLC ±-
ANGLES ±1°

MATERIAL 1

FINISH - -

DWN S. SHINDE 30JUL2021
CHK D. SWARTZ 30JUL2021
APVD V. SHETTAR 30JUL2021

PRODUCT SPEC 108-143081
APPLICATION SPEC 114-143082
WEIGHT -

TE Connectivity

PRELIMINARY

NAME ASSEMBLY, CAP, PANEL MOUNT, POWER VERSA-LOCK

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A1 | 00779 | C-2391577 | - |

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV 1

4805 (3/13)

Downloaded from Arrow.com.