

Specification Sheet

Part Number: 201-20010

An innovative coupling system allows for an unlimited number of bundling combinations.

Clips can be easily released and reused.

Clips swivel freely which reduces mechanical stress and eliminates pinch points.

High Impact Polyamide 6.6 material provides firm fit even in rugged conditions.

Consists of acrylate adhesive with base of polyurethane foam allowing it to adhere firmly and easily to nearly any surface.



Protective Strap for Helawrap HWCLIP25 and HWCLIP30, Black, PVC, 500/pkg

Article Number	201-20010
----------------	-----------

Type	R1
------	----

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size, therefore allowing the R1 protective strap to hold wires down effortlessly. Different cable sizes can be bundled together, organized and protected flexibly and efficiently.
---------------------	---

Short Description	Protective Strap for Helawrap HWCLIP25 and HWCLIP30, Black, PVC, 500/pkg
Global Part Name	R1-PVC-BK
Length L (Imperial)	0.63
Length L (Metric)	16.0
Fixation Method	screwable
Width W (Imperial)	0.94
Width W (Metric)	23.8
Bundle Diameter Min (Metric)	1.0
Height H (Imperial)	0.13
Height H (Metric)	3.2
Material	Flexible Polyvinyl Chloride, cadmium free (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-2
Halogen Free	No

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-31°F to +122°F (-35°C to +50°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)