



7012AJX Product Details

[Share](#) [Print](#) [Email](#)


7012AJX

(2-1423157-3)

TE Internal Number: 2-1423157-3

 [Active](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 7000 Electropneumatic Timing - Industrial Series
- Input Voltage = 110 VAC, 120 VAC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 240 VAC
- Mounting Options = Panel Mount

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = 7000 Electropneumatic Timing - Industrial
- Termination Type = Screw Terminal

Electrical Characteristics:

- Input Voltage (VAC) = 110, 120
- Contact Rating = 10A @ 240 VAC

Contact Features:

- Mounting Options = Panel Mount
- Mode of Operation = On-Delay
- Delay Time = 3 cycle. to 120 cycle.
- Type of Control = Knob
- Repeatability, Max. = $\pm 10\%$
- Option = Hardware and Adjustment for Horizontal Operation
- Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

Configuration Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = -30 - +75

Other:

- Brand = Agastat

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

