



Sensing and Control

Honeywell.com (<http://www.honeywell.com>)
Test & Measurement
(<https://measurementsensors.honeywell.com/>)

Search the entire website and product database

Start Here ... Search
HOME (/sensinghome) ABOUT US (/about honeywell sensing and control) KEY INDUSTRIES SERVED (/industries) PRODUCTS & INFORMATION (/products & information) NEWS & EVENTS (/index.php?ci_id=2533&la_id=1) SALES & SUPPORT (/index.php?ci_id=2596&la_id=1) LOGIN (/login)

LSXP3K3

(Home (/index.php?ci_id=3972&la_id=1) : Products (/products) : basics : Switches : MICRO SWITCH™ Hazardous Location Switches : LSX)

Distributor Inventory

Input part number for stock availability



Lever NOT included

Actual product
appearance may vary.

Explosion-Proof Limit Switches LSX Non Plug-in: Side Rotary; 1NC 1NO SPDT
Snap Action; 0.5 in - 14NPT conduit

Sales & Service

Distributor Inventory

Narrow Your Search**Modify Your Search****Products**

Select Option

Technology

Select Option

Industries Served

Select Option

Overview **Specs** Documentation Application Notes

Product Specifications

Availability	Global
Operating Force (OF)	0.45 Nm [4 in lb] max.
Pretravel (PT)	9° max.
Overtravel (OT)	66° min.
Differential Travel (DT)	3° max.
Product Type	MICRO SWITCH™ Weather-Sealed, Explosion-Proof Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	1NC 1NO SPDT Snap Action, Double-Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	LSX Non Plug-in
Series Name	LSX
Sealing	NEMA 1, 3, 4, 6, 7 (Class 1, Division 1, Groups B, C, D), 9 (Class 2, Division 1, Groups E, F, G), 13
CSA File #	LR57327
UL File #	E61730
Operating Temperature	-12 °C to 121 °C [10 °F to 250 °F]
Comment	Head assembled with actuator shaft to right side; Low Differential Travel
Agency Approvals and Standards	UL, CSA
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Explosion-proof

Product Search

Product Type: All Product Types

Industry: All Industries

Search Term: Start Here ...

☐ New Products Only☒ Entire Product Catalog

Search

My Links

eCOM Login (/index.php?ci_id=50629&la_id=1)
Request Access to eCOM (/ecom access request)
Rep/AD Portal Login (/index.php?ci_id=50606&la_id=1)
Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1)
Sample Request (/samplerequest)
Digital University Login (/index.php?ci_id=50607&la_id=1)
Limitless Microsite (/index.php?ci_id=50631&la_id=1)
Supply Microsite (/index.php?ci_id=44887&la_id=1)

Literature and Media

Data Sheets (/white paper and technical data sheets library)
Videos (/videos)
Literature (/literature)
Literature Request (/index.php?ci_id=50636&la_id=1)
White Papers (/whitepapers)
Application Notes (/application notes)
Application Demos (/index.php?ci_id=141383&la_id=1)
CAD Renderings (/cad renderings)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)
Technical Support (/index.php?ci_id=50609&la_id=1)
Global Sales & Service (/index.php?ci_id=50610&la_id=1)
Website Feedback (/index.php?ci_id=142628&la_id=1)

 <http://www.youtube.com/user/ArrowSensorsAndControl>

[Terms & Conditions \(/index.php?ci_id=2588&la_id=1\)](/index.php?ci_id=2588&la_id=1)

[Privacy Statement \(/index.php?ci_id=2589&la_id=1\)](/index.php?ci_id=2589&la_id=1)

[Site Map \(/sitemap\)](/sitemap)