



Part Number : [1502010005](#)
Product Description : Ditto Hermaphroditic Crimp Housing, Positive Lock, 5 Circuit, Glow-Wire Capable, Natural
Series Number : 150201
Status : Obsolete
Product Category : Connector Housings



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	150201
Description	Ditto Hermaphroditic Crimp Housing, Positive Lock, 5 Circuit, Glow-Wire Capable, Natural
Application	Power, Wire-to-Wire
Product Name	Ditto
UPC	889056215763

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	5
Color - Resin	Natural (White)
Flammability	94V-2
Gender	Hermaphroditic
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.467/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +80°C, See Product Specification