Part Number : 191600039
Product Description : Twist Lock Splice for 22-14 AWG Wire, Grey, Carton
Series Number : 19160
Status : Active
Product Category : Splices
Engineering Part Number : TL-G



Documents and Resources

Drawings

191600039_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19160
Description	Twist Lock Splice for 22-14 AWG Wire, Grey, Carton
Product Name	Closed-End Twist Lock
Style	Twist Lock
Type	Closed-end Connector
UPC	800753110434

Agency

CSA	LR700095
UL	E32244

Electrical

Voltage - Maximum	300V

Physical

Barrel Type	Closed
Color - Resin	Gray
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.431/g
Packaging Type	Carton

Downloaded from Arrow.com.

Temperature Range - Operating	-40 to 105°C
Wire Insulation Diameter	6.60mm max.
Wire Size (AWG)	14, 16, 18, 20, 22
Wire Size mm^2	0.324-2.08

Downloaded from Arrow.com.