

You are here: Home

- Home
- Surface Mount Products ▶
- X2Y Products ▶
- Leaded Capacitors ▶
- High Temp Capacitors ▶
- Technical Notes ▶
- Prototyping Kits ▶
- View Product Catalog
- Product Training
- Environmental Compliance ▶
- Distributor Inventory

Part Number Search

part number...

Go

Parameter Search

Volt

Size

Cap Value

Go

Reset



Match Info	Matching Parts and Available Actions:	
5487BP15B675E OffsiteMatch	Band-Pass Filters, 2.45 GHz EIA 0603-2520, 1810 MHz - 2593 MHz Links will send you to our partner company, Johanson Technology Search Distributor Inventory	Datasheet
	Band-Pass Filters, 5.5 GHz EIA 0805, 5450 MHz - 5515 MHz Links will send you to our partner company, Johanson Technology Search Distributor Inventory	Datasheet
	Band-Pass Filters, Other EIA 0402-2520, 1810 MHz - 7160 MHz Links will send you to our partner company, Johanson Technology Search Distributor Inventory	Datasheet

About	Technical Notes	Products	Support	
- Contact Info - Company Info - Sales Rep - Distributors - Careers - RoHS Compliance	- General - Application Notes - Processing - Environmental - X2Y Applications - Product training	- Surface Mount - X2Y technology - Prototyping Kits - Leaded Capacitors - High Temp Capacitors - Full Product Catalog	- Quote Request - Sample Request - Prototyping Kit Request - Hard literature Request - Ask a Technical Question - Purchasing Terms and Conditions	Johanson Dielectrics johansondielectrics.com 15191 Bledsoe St. Sylmar, CA 91342 818-364-9800 phone 818-364-6100 fax