

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530042

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA 5-15, 15A, 120V, 0.61m (2.0') Cord Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification	
CSA	LR6837
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Name	Safeway
Receptacle Type	N/A
Taxonomy	Power Distribution
Type	GFCI Commercial Duty, Single Phase
UPC	78678828405
Physical	
Cord Diameter	9.40mm (.370")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag
Electrical	
Cord Type	14/3 SJTW
Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	120V AC
Material Info	
Engineering Number	15051-1
Reference - Drawing Numbers	
Sales Drawing	1301530045-000

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

130153 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION