

**Part Number :** [1300950172](#)

**Product Description :** Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Short Mesh Length 0.533m (21.00"), Approximate Break Strength 2041.17kg (4500 lbs)

**Series Number :** 130095

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 35940



---

## Documents and Resources

### Drawings

[1300950172\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | Cable Grips   |
| Series       | 130095  |
| Description  | Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Short Mesh Length 0.533m (21.00"), Approximate Break Strength 2041.17kg (4500 lbs) |
| Comments     | Cable Eye Thickness 7/32"   |
| Product Name | Medium Duty   |
| Type         | Pulling Grip  |
| UPC          | 78678835940   |

#### Agency

|     |         |
|-----|---------|
| CSA | LR32159 |
|-----|---------|

#### Physical

|                            |                            |
|----------------------------|----------------------------|
| Approximate Break Strength | 2041.17kg (4500 lbs)       |
| Bale Length                | N/A                        |
| Body Style                 | Straight                   |
| Cable Diameter             | 12.70-15.49mm (.500-.610") |
| Color - Grommet            | N/A                        |
| Eye Type                   | Flexible                   |
| Gender                     | N/A                        |
| Material - Body            | N/A                        |
| Material - Grip            | Galvanized Steel           |
| Mesh Length                | 0.533m (21.00")            |
| Number of Holes            | N/A                        |
| O-Ring                     | N/A                        |

|             |     |
|-------------|-----|
| Thread Size | N/A |
|-------------|-----|

---

This document was generated on May 24, 2026