Part Number : 192130008
Product Description : Avikrimp Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Series Number : 19213
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : WP-8210T
Packaging Alternative : 192130007 (Bag)

Documents and Resources

Drawings

192130008_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19213
Description	Avikrimp Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 10.40mm
Product Name	Wire Pin,Avikrimp
UPC	800753053489

Agency

CSA	LR18689
UL	E32244

Physical

Flammability	94V-2
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	2.203/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	1.016µm

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	6.35mm max.
Wire Size (AWG)	10, 12
Wire Size mm^2	N/A

Application Tooling

Global

Description	Part Number
Mini-Mac Pneumatic Applicator for Industrial Terminals 26-6 AWG	638851500

Downloaded from Arrow.com.