

# WT-R HF 4,8X200 - Cable tie

3240803

<https://www.phoenixcontact.com/us/products/3240803>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders, with molded body-bound rivet, also ideally suited to restricted installation dimensions

## Commercial data

Item number	3240803
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE07
Product key	BE7133
Catalog page	Page 619 (C-3-2019)
GTIN	4046356705417
Weight per piece (including packing)	1.53 g
Weight per piece (excluding packing)	1.45 g
Customs tariff number	39269097
Country of origin	HR

# WT-R HF 4,8X200 - Cable tie

3240803

<https://www.phoenixcontact.com/us/products/3240803>



## Technical data

### Product properties

Product type	Cable tie
Type	Internal teeth
Tensile strength GRP	220 N

### Dimensions

Width	4.8 mm
Length	200 mm
Hole diameter	6.3 mm
Max. material thickness	3 mm

### Material specifications

Color	transparent
Material	PA 6.6
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Cable/line

External cable diameter	2 mm ... 50 mm
Tensile strength	220 N

### Environmental and real-life conditions

#### Ambient conditions

Optimum ambient temperature (storage/transport)	23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	no

### Mounting

Mounting type	Cannot be removed
	Snap in

# WT-R HF 4,8X200 - Cable tie



3240803

<https://www.phoenixcontact.com/us/products/3240803>

## Classifications

### ECLASS

ECLASS-13.0	27140702
-------------	----------

### ETIM

ETIM 9.0	EC000046
----------	----------

### UNSPSC

UNSPSC 21.0	39121700
-------------	----------

# WT-R HF 4,8X200 - Cable tie



3240803

<https://www.phoenixcontact.com/us/products/3240803>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)