



Part Number : [2280060001](#)
Product Description : Mega-Fit Connector Position Assurance (CPA) Retainer, UL 94V-0, Red
Series Number : 228006
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[2280060001_sd.pdf](#)
[2280061000-PK-000.pdf](#)

3D Models and Design Files


[2280060001_stp.zip](#)

Specifications

[768232000-AS-000.pdf](#)
[1054171000-PS-000.pdf](#)
[1720631000-PS-000.pdf](#)
[1720631000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	228006
Description	Mega-Fit Connector Position Assurance (CPA) Retainer, UL 94V-0, Red
Component Type	Connector Position Assurance
Product Name	Mega-Fit
UPC	198282697916

Physical

Circuits (Loaded)	0
Circuits (maximum)	0
Color - Resin	Red
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.230/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Mega-Fit Tangless TPA-Capable Single Row Receptacle Housings	<u>200456</u>

This document was generated on Jun 15, 2025