Data Sheet | Item Number: 282-387

End and separator plate; 1.5 mm thick; with lock-out seal option; orange

https://www.wago.com/282-387



Color: orange

Physical data	
Width	1.5 mm / 0.059 inches
Height	122 mm / 4.803 inches
Depth	71.7 mm / 2.823 inches

Material data	
Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.255 MJ
Weight	9.6 g

Environmental requirements	
Processing temperature	-35 … +85 °C
Continuous operating temperature	-60 … +105 °C

Commercial data	
Product Group	1 (Rail Mounted Terminal Blocks)
PU (SPU)	50 (10) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332264907
Customs tariff number	85389099990

Downloaded from Arrow.com.

Product Classification

UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 282-387

Documentation

Bid Text

282-387	19.02.2019	xml 2.65 KB	
282-387	03.03.2017	doc 23.50 KB	

CAD/CAE-Data

CAD data

2D/3D Models 282-387


CAE data

EPLAN Data Portal 282-387

WSCAD Universe 282-387

ZUKEN Portal 282-387

Installation Notes



A lock-out seal can be used on the disconnect link in notched “I” position.

Downloaded from Arrow.com.