



Representative Image

Alternate Catalog No. ABP 3350

Catalog No. ABP3350

Description: TRANS EYEBOLT CON 12-350 5/8X4 3OUT

UPC No 783786686216

[Home](#) > [Connectivity & Grounding](#) > [Homac](#) > [Wire connectors](#)

Aluminum Overhead Transformer Eyebolt Multi-Tap Set Screw Connectors, length 4-1/8 inch, stud size 5/8 X 4 , cable range #12-350 kcmil, outlets 3.

Descriptors

Category	Wire connectors
Special Features	Made from high strength Aluminum alloy to maintain constant bolting pressure on conductors. Screws designed for optimum electrical connection and maximum conductor-contact pressure. Dual rated for use with aluminum and copper conductors. Designed with factory mounted 90 degree angle copper studs for installation in pole-type transformers with secondary eyebolt connections.
Application	Designed with factory-mounted 90 Degree angle copper studs for installation in pole-type transformers with secondary eyebolt connections.

Specifications

Connection	Mechanical
Number Of Conductors	3
Material	Aluminum
Finish	Bare
Insulation	None
Temperature Rating	up to 90 C
Environmental Conditions	All Seasons / Conditions

Classifications

Brand Name	Homac
Standard	ANSI C119.4

Dimensions

Size	4-1/8 inch long, Stud Size 5/8 X 4
Wire Size	#12 to 350 kcmil

by ABB