
Part Number : 1201089125
Product Description : Micro-Change (M12) Double-Ended Cordset, 8-Pole X-Coded Male (Straight) to 4-Pole D-Coded Male (Straight), 24 AWG, Teal TPE Cable, 10.0m (32.81') Length
Series Number : 120108
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E12A06004M100



Documents and Resources

Drawings

1201089125_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; 6,6'-Di-tert-butyl-2,2'-methylenedi-p-cresol per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120108
Description	Micro-Change (M12) Double-Ended Cordset, 8-Pole X-Coded Male (Straight) to 4-Pole D-Coded Male (Straight), 24 AWG, Teal TPE Cable, 10.0m (32.81') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	196823082566

Agency

UL	E361772

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Male-Male
Keyway	D-Coded, X-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	429.000/g
Orientation	Straight to Straight
Poles	4, 8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24

Downloaded from Arrow.com.