

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301110030

Status:

Active

Overview:

Stringlights

Description:

Safety Yellow Molded Stringlight, 200W, 12/3 SJTW with 2.43m Lead, 10 Sockets, Full Ground Ring, Overall Length 30.48m (100.0')

Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E112216
General	
Product Family	Portable Lighting
Series	130111
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Safety Yellow
Type	String Lights
UPC	78678840869
Physical	
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Depth	N/A
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	30.48m (100.0')
Material - Guard	N/A
Mounting Style	Stringer
Net Weight	2.700/kg
Packaging Type	Carton
Socket Construction	Molded
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/3 SJTW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	5002



EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130111 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION