

# Product data sheet

Specifications



## APC NetShelter Rack PDU, Switched, 0U, 5.0kW 200V and 208V 30A, (21) C13/C15 and (3) C19/C21 outlets

APDU9941

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Colour	Black
Product or component type	PDU
PDU type	Switched
Cord length	3.05 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets Safety guide

### Complementary

Input Voltage	208 V 200 V
Height	182.9 cm
Width	5.5 cm
Output Voltage	200 V 208 V
Depth	4.6 cm
Product weight	8.5 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	NEMA L6-30P
Mounting mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Communication port protocol	SNMP Redfish
[In] rated current	24 A
Max line current	30 A
Input current limits	30 A
Load capacity	4992 VA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Network frequency	50/60 Hz
Outlet type and quantity	21C13/C15 3C19/C21
Communication network type	10/100/1000BASE-T

## Environment

Product certifications	cUL listed FCC part 15 class A PSE
Standards	ICES-003
Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.0000000000...15240.0000000000 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	204 cm
Package 1 Width	12.4 cm
Package 1 Length	16.5 cm
Package 1 Weight	10 kg

## Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>

Image of product / Alternate images

Alternative

---

