

HPP V4 USB 3.0 A, C-PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 245 1904
Specification	HPP V4 USB 3.0 A, C-PFT
HARTING eCatalogue	https://b2b.harting.com/09452451904

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	USB
Element	Panel feed through
Specification	USB 3.0 type A
Description of hood/housing	Compact

Version

Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	15.2 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)