






PRODUCT NUMBER	PITCH
V7xx71x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Female contact: PhBz(CuSn), Tin plated
- Item ③ Terminal cover: Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 

PART NO.: V7 xx 7 1 x 0 00J0 G

DIM		TOL				
		2P-5P	6P-10P	11P-15P	16P-20P	21P-24P
Dim L	Nx5.0+2.0	±0.15	±0.20	±0.25	±0.30	±0.40
Dim B	(N-1)x5.0	±0.15	±0.20	±0.25	±0.30	±0.40
Dim C	Nx5.0	0 -0.20		0 -0.30		
Dim D	(N-1)x5.0	±0.15	±0.20	±0.25	±0.30	±0.40

Solid block
No. of poles
02 2poles
03 3poles
...
24 24poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK		
					angles	MM	title		
					0.05		TERMINAL BLOCK		
					X±1°		PLUGGABLE PCB PLUG, VERTICAL		
					dr	EVIN ZHONG 043014	dwg no		
					enr	EVIN ZHONG 043014	sheet 1 of 1 size		
					chr	HANKE FENG 043014	V7xx71x000J0G		
					appd	SHI JUN 043014	A4		
sheet index				revision	A		type		
				sheet	1		CUSTOMER Drawing		