






Circuits	Dimension	
	A	B
4	8.45	2.54
6	10.99	5.08
8	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48



Specifications:

Current rating:1.5A AC,DC
Voltage rating:230V AC, DC
Contact tesistance:20m ohm Max
Insulation resistance:1000M ohm Min
Withstanding voltage:AC 500V AC/minute
Operating Temperature:-40°C ~ +105°C
Materials and Finish
Insulator:PBT(UL94V-0)
Insulator Color:Red
Contact material:Phosphor Bronze
Finish:Tin Plated

How to Order


TMM-X-X-XX-X

Type
1-IDC Male
2-IDC Plug
3-DIP Male Straight
4-DIP Female Straight
5-DIP Female R/A
6-SMT Female Straight

Packaging
1 - Tape & Reel with vacuum cap
2 - Tube
3 - Bag
4- Tape&Reel without vacuum cap

Number of Positions
04, 06, 08, 10, 12, 14,
16, 18, 20, 22, 24 or 26

Locking System
0-without lock
L-with lock



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Series IDC Male	Amphenol European Design Center
X.X ±0.2	CHECKED Rob	2009/10/07		
X.XX ±0.15	APPROVED Rob	2009/10/07		
UNLESS OTHERWISE SPECIFIED	UNIT : mm	SIZE : A4	DRAWING N° TMM-1-0-XX-X	Scale N.A. Sheet 1 of 1
				REV. E