
1743654-1 ! PENDING OBSOLESCENCE

TE Internal #: 1743654-1

TE Internal Description: 090III MLC REC(S) CONT MULTILOCK, RECEPTACLE AND TAB

View on TE.com >



All MULTILOCK, RECEPTACLE AND TAB (81)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

Downloaded from Arrow.com.




TE Part # 936095-3
090III 20P PLUG ASSY L-GRY




TE Part # 368454-1
090/250 HYB 16P PLUG ASS'Y



TE Part # CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING




TE Part # 368088-1
090II NON SLD TAB(SQ 0.3-0.5)



TE Part # 368457-1
090/250 HYB 20P PLUG ASSY



TE Part # 1743037-2
HYBRID 92P PLUG ASSY



TE Part # 936233-8
090III 8P PLUG ASSY BLUE



TE Part # 368451-1
090/250 HYB 14P PLUG ASS'Y



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

Customers Also Bought



TE Part #1897015-2
MT-2/JPT SLD 26P CAP COVER



TE Part #2066010-1
2P SUPERSEAL 1.5 SRS PLUG ASSY BLACK



TE Part #2005479-6
PCU 105P RETAINER HSG-MCON 1.2 MM



TE Part #953318-2
1W HSG FOR DIESEL PLUG

TE Part #2307646-1
TPA TAB HSG,8POS,ECONOSEAL


TE Part #2307642-1
8POS,ECONOSEAL,REC HSG ASSY, SLD

TE Part #1203559-1
DUAL EXTERNAL RELAY BASE MICRO (FR)




TE Part #1801618-1
RELAY 40A HOLDER

Downloaded from Arrow.com.



TE Part #368539-1
070 MLC PLUG HSG 6P(D.B)



TE Part #1743656-1
090III MLC REC(L) CONT

Documents

Product Drawings

090III MLC REC(S) CONT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1743654-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1743654-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1743654-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

MULTILOCK Connector System

English

Product Specifications

Application Specification

English

Downloaded from Arrow.com.