

03

SV ... C



Circular connectors with threaded joint M16 acc. to IEC 61076-2-106, IP40/IP68



Plug acc. to IEC 61076-2-106, IP40, straight version, with threaded joint, empty housing for reception of crimp contacts, with bend protection, for cable diameter up to 6 mm

03

SV ... C



Environmental conditions

Temperature range -40 °C/+85 °C

Materials

Insulating body	PA GF, V-0 according to UL94
Shielding contact	CuZn, pre-nickel and tin-plated
Sleeve	PC, HB according to UL94
Strain relief	steel, nickel-plated
Housing	CuZn, nickel-plated
Knurled screw	CuZn, nickel-plated
Bend protection sleeve	TPE
Screw	steel, nickel-plated

Mechanical data

Tightening torque connector 1–3 Nm
Protection class IP40¹

¹ according to IEC DIN EN 60529, only in locked condition with an appropriate counterpart

Connectable conductors for crimp area

Cable diameter 4–6 mm


Electrical data (at T_{amb} 20 °C)

Rated current	5 A (T _{amb} 40 °C)
Rated voltage	with pollution degree 1: 300 V (versions 30, 40, 50/6, 60, 70) 100 V (versions 50, 71, 80, 81) with pollution degree 2: 250 V (versions 30, 40) 32 V (versions 50, 71, 80, 81) 160 V (versions 50/6, 60, 70)
Rated impulse voltage	1500 V (versions 30, 40, 50/6, 60, 70) 500 V (versions 50, 71, 80, 81)
Material group	II (IEC)/I (UL) (400 ≤ CTI < 600)
Overvoltage category	I
Insulation resistance	> 100 MΩ


Associated products

Counterparts		
☞ 030398	☞ KFR	☞ KfV
☞ KfV ... C	☞ KGR	☞ KGV
☞ KGV ... C	☞ KV	☞ KV ... C
☞ KV ...-8	☞ KV ...-8 C	☞ WKV


Pin configurations, crimp side view




03-a
SV 30 C




04-a
SV 40 C




05-b
SV 50 C




05-a
SV 50/6 C




06-a
SV 60 C



07-a
SV 70 C



07-b
SV 71 C



08-a
SV 81 C

[☞ WKV ... C](#)

Accessories

[☞ 0369](#)

[☞ 0383](#)

[☞ 038399](#)

[☞ 038899](#)

03

SV ... C

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
SV 30 C	3	50	100
SV 40 C	4	50	100
SV 50 C	5	50	100
SV 50/6 C	5	50	100
SV 60 C	6	50	100
SV 70 C	7	50	100
SV 71 C	7	50	100
SV 81 C	8	50	100

Packaging:

unassembled, individually in a plastic bag, in a cardboard box