



Ordinary "included in the box" video cables often use low quality materials with inferior shielding that can result in poor picture quality. But this s-video/composite video cable delivers all the detail, color and brightness you expect from your audio/video equipment. Gold-plated terminals ensure long-lasting, corrosion-free connections.

Each video component is constructed from 75 Ohm coaxial cable that delivers clear, crisp video images, and is individually double-shielded with foil and braid shield to reduce unwanted noise and distortion. The dual coax design keeps the black and white (Y) signal separate and combines the color signals into a single color signal (C) to provide better picture quality than a composite cable.

high quality 26 AWG audio wire 90% spiral-wrapped with tinned copper to provide shielding against EMI/RFI interference. Fully molded connectors provide excellent strain relief to keep your cable intact while the PVC jacket provides added flexibility and durability.

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120291565	Country Of Origin	China
Compliance	CE, RoHS	Application Sector	Commercial, Residential
Type	Cable		

Dimensions

Cable Length	50 ft
--------------	-------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Plating Specification	Gold
Signal Transmission	Bidirectional	Cable Type	Audio, Video
Jacket Rating	Standard / Non-Rated	Connector 2	RCA Composite Video Male, RCA Stereo Audio Male, S-Video Male

Connector 1	RCA Composite Video Male, RCA Stereo Audio Male, S-Video Male
-------------	--
