

Specification Sheet

Part Number: 156-00069



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Article Number	156-00069
Type	WSIFT9A
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
Short Description	Heavy Duty Cable Tie with Fir Tree Mount, 15"L, 0.03 - 0.25" Panel Thick, PA66HIRHSUV, Black, 100/pkg
Global Part Name	WSIFT9A-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.0
Length L (Metric)	387.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.3
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.37
Bundle Diameter Min (Metric)	9.5
Bundle Diameter Max (Imperial)	3.25
Bundle Diameter Max (Metric)	82.5
Height H (Imperial)	.75
Height H (Metric)	19.10

Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	6.5
Mounting Hole Diameter D (Imperial)	0.34 - 0.36 "
Mounting Hole Diameter D (Metric)	8.7 - 9.2 mm
Mounting Hole Diameter D Min (Imperial)	0.34
Mounting Hole Diameter D Max (Imperial)	0.36
Mounting Hole Diameter D Max (Metric)	9.2
Disc Diameter (Metric)	21.6
Disc Diameter (Imperial)	0.85
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)