



Part Number : 1301040021

Series Number : 130104

Product Category : Lamps and Lights

Product Description : Haztex Hazardous Location 26W Fluorescent Hand Lamp Only

Status : Active

Engineering Number : 1090-HZ

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130104
Description	Haztex Hazardous Location 26W Fluorescent Hand Lamp Only

Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	N/A
Product Family	Specialty Lighting
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861277

Agency

UL	E30252
----	--------

Electrical

Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	100.08mm (3.940")
Duty	Hazardous
Guard Included	Yes
Guard Type	Cast Aluminum
Height	482.60mm (19.000")
Lamp Type	PL-C 26/41/4P
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Net Weight	2322.392/g
Outlet	None

Packaging Type	Carton
----------------	--------

This document was generated on Jul 06, 2024