



Part Number : [1301530188](#)
Product Description : Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, NEMA L6-30, 30A, 240V, 7.62m (25.0') Cord Length
Series Number : 130153
Status : Active
Product Category : Power Distribution
Engineering Part Number : 30053-25M



Documents and Resources

Drawings
[1301530188 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, NEMA L6-30, 30A, 240V, 7.62m (25.0') Cord Length
Enclosure Rating	NEMA 6P
NEMA Configuration	NEMA L6-30
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678889722

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	30.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	240V

Physical

Cord Diameter	13.00mm (.512")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	7.62m (25.0')
Cord Type	10/3 SJEOOW

Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on May 21, 2026