


REV.	DATE	ECR NO.	DESCRIPTION
NC	11/25/08	—	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex											
7						DRAWN	GRS	11/25/08													
6						CHECKED															
5	CONTACT PIN	BRASS	GOLD	1			ISSUED				PART DESCRIPTION										
4	CONTACT PIN	PHOS. BRONZE	GOLD	1			SHEET	1 OF 1				TNC "T" ADAPTER JACK–PLUG–JACK									
3	INSULATOR	DELRIN	NATURAL	2								PART NO.									
2	BODY	BRASS	NICKEL	1								122356									
1	SHELL/HOUSING	BRASS	NICKEL	1			CAD FILE					DWG. NO.		122356.DWG		REV.	NC	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY			C:/122/122356.DWG														