**Part Number :** 936000351
**Product Description :** Heavy-Duty Plastic Gable Gland with Gasket, M20x1.5 Thread, Light Grey RAL 7035
**Series Number :** 93600
**Status :** Active
**Product Category :** Heavy-Duty Cable Glands
**Engineering Part Number :** 7000.7823.2



## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Cable Glands |
| Series | 93600 |
| Description | Heavy-Duty Plastic Gable Gland with Gasket, M20x1.5 Thread, Light Grey RAL 7035 |
| Cable Gland Type | IP68 with Gasket |
| IP Rating | IP68 |
| Product Name | Heavy-Duty Connectors |
| Standard | DIN EN 50262, EN 60529 |
| UPC | 887191852232 |

### Physical

| | |
|---|---|
| Cable Diameter | 6.00-12.00mm |
| Gland Color | Light Grey RAL 7035 |
| Material - Cable Gland | Polyamide |
| Material - Gasket | NBR |
| Material - Nut | Polyamide |
| Packaging Type | Bag |
| Panel Cutout Diameter | 20.50mm |
| Panel Mount | Yes |
| Temperature Range - Operating | -40° to +100°C |
| Thread Size | M20x1.5 |
| Thread Type | (M) Metric |
| Waterproof / Dustproof | Yes |
| Waterproof / Dustproof Type | IP68 |

## Mates With / Use With

### Use with Part(s)

Downloaded from Arrow.com.

| Description | Part Number |
| --- | --- |
| Use With | Sealed Enclosures and Boxes |



Downloaded from Arrow.com.