HellermannTyton

Technical data sheet

Article number:
321-30000 HA67-19.0/3.2



Product Group	Heat shrinkable tubing 6:1, adhesive lined in 1.2 m cuts
Product Family	HA67 - thick wall adhesive lined
Material	Polyolefin, cross-linked (PO-X)
Colour	Black (BK)

Adhesive	Hot melt adhesive
Dielectric Strength [Test method]	20 kV/mm [IEC 243]
Elongation at break (min.)	400 %
Longitudinal Change After Shrinkage	-10% max.
Min. Shrink Temperature - °C	+120 °C
Operating Temperature	-55 °C to +110 °C
Package Content	10 pcs.
Package Content packed in	pack
Recov. Ø d max.	3.2 mm
Shrink Ratio	6:1
Supplied Ø D min.	19.0 mm
Tensile Strength	14 MPa
UV-Stabilised	No
Wall (WT)	3.2 mm

HF ✓ RoHS ✓

created on 15. May 2026, 5:32 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.