



T 3301 002 U

Description

Female cable connector 4 pole  
IP40; solder; silver; straight;  
screwlocking

IP-class mated

IP40

number of positions (w/o PE)

4

rated current (40 °C)

5 (A)

rated voltage

300 (V)

● active

Please log in to receive your price.

50 pcs.

The minimum order amount is 50 pcs.;  
packing unit 50 pcs.  
Check availability

- add to cart
- add to favorite
- send request

Technical data

Downloads

| General Characteristics      |      |                        |
|------------------------------|------|------------------------|
| contact diameter             |      | 1,5 mm                 |
| gender                       |      | female                 |
| IP-class mated               |      | IP40                   |
| maximum cable diameter       | (MM) | 8                      |
| minimum cable diameter       | (MM) | 6                      |
| number of positions (w/o PE) |      | 4                      |
| part category                |      | female cable connector |
| termination                  |      | solder pin             |
| Further Characteristics      |      |                        |
| max. wire gauge              |      | 0.5                    |
| min. wire gauge              |      | 0.05                   |
| RoHS Compliant Yes           |      | X                      |
| Electrical Characteristics   |      |                        |
| rated current (40 °C)        | (A)  | 5                      |
| rated voltage                | (V)  | 300                    |