

Specification Sheet

Part Number: 151-00982

Integrated design allows for easy insertion by hand.

1.0 - 3.0 mm panel thickness range allows for multiple applications.

Double-compression design can accommodate up to 2 wires or cables of varying sizes.

Presents a high extraction force for withstanding extreme conditions.



Heavy Duty Metal Edge Clip, 1 - 3mm Panel Thickness, 5 - 7.6mm Cable Range, SS304, 100/bg

Article Number 151-00982

Type MSC2

Color Metal (ML)

Quantity Per pack

Product Description HellermannTyton's Heavy Duty Metal Edge Clip provides an excellent alternative to managing up to 2 wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Heavy Duty Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. This Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Short Description	Heavy Duty Metal Edge Clip, 1 - 3mm Panel Thickness, 5 - 7.6mm Cable Range, SS304, 100/bg
Global Part Name	MSC2-SS304-ML
Length L (Imperial)	0.95
Length L (Metric)	24.1
Fixation Method	Edge Clip
Width W (Imperial)	0.50
Width W (Metric)	13.0
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	0.30
Bundle Diameter Max (Metric)	7.59
Depth D (Imperial)	0.861
Depth D (Metric)	21.90
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0

Panel Thickness Max (Metric)	3.0
Material	Stainless Steel (SS304)
Material Shortcut	SS304
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Customs Number

7326908695

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)