


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

WIRE MAPPING


RJ45



12345678


PAIR 1 = WHITE
2 = ORANGE
3 = WHITE
PAIR 4 = BLUE
5 = WHITE
6 = GREEN
PAIR 7 = WHITE
8 = BROWN

X-CODE



PAIR 1 = WHITE
2 = ORANGE
PAIR 3 = WHITE
4 = GREEN
PAIR 5 = WHITE
6 = BROWN
PAIR 7 = WHITE
8 = BLUE

TWIST TIE



RJ45

X-CODE

NOTES:

1. PART NUMBER: ICX44T1NBL*M
2. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. CABLE MEETS CATEGORY 6 REQUIREMENTS.
5. ALL MATERIALS AND COMPOUNDS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
6. PART AVAILABLE IN 1M, 2M LENGTHS.

TITLE
INDUSTRIALNET PATCH CORD, M12 X-CODE FEMALE / RJ45, CATEGORY 6

CUSTOMER DRAWING

ITEM REVISION NAME

00106BAZ/00


DATASET FILE NAME

00106BAZ_DC/00B

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±
.XX ±

.XXX ±
ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

N/A

DRAWING NUMBER:

00106BAZ

00B	2/9/18	JBO	MGH	MARK	RELEASED TO PRODUCTION	00106BAZ
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
JBO	12/18/17	MGH	NONE		A