




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Technology	Electro-Mechanical	
Resonant Frequency	2,300	(Hz)
Rated Voltage	6	(V)
SPL @ 10cm	85	(dBA)
Tone	Single Tone	
Mount Type	Thru Hole	
Voltage Range	4 ~ 8	(V)
Max Rated Current	30	(mA)
Housing Material	NORYL	
Operating Temperature	-40 ~ +85	°C
Storage Temperature	-40 ~ +85	°C
Weight	7	(g)

## Notes

- 1) All dimensions are in mm unless otherwise noted
- 2) All parts meet RoHS



DB UNLIMITED

Electro-Mechanical Indicator

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			10/21/2013	J.S

IE162306-1