



## NetManager™ HC Horizontal Single-Sided Manager, 3RU, White

NMF3WH

The NetManager™ High Capacity Horizontal Cable Manager cost-effectively organizes and protects copper and fiber network cabling in any standard EIA 19 inch (483mm) rack or cabinet. Large front finger openings easily accommodate Cat 6 and 6A cables, reducing installation time and maintenance costs. The single-sided manager is 3 RU and has a hinged front cover only. The manager is white.

### Specifications

|                        |                                    |
|------------------------|------------------------------------|
| Product Type           | Single-Sided Manager               |
| Compatible Rack System | 19                                 |
| Body Material          | ABS                                |
| Orientation            | Horizontal                         |
| Cover Material         | PVC                                |
| Finger Material        | ABS                                |
| Sub Brand              | NetManager™ High Capacity          |
| Overall Depth (In.)    | 6.2                                |
| Overall Depth (mm)     | 157                                |
| Overall Width (In.)    | 19                                 |
| Overall Width (mm)     | 483                                |
| Overall Height (In.)   | 5.2                                |
| Overall Height (mm)    | 133                                |
| Number of Rack Units   | 3                                  |
| Environment            | Indoor                             |
| Color                  | White                              |
| Standards Met          | RoHS Compliant                     |
| For Use With           | Standard 19" mount rack or cabinet |
| Includes               | Manager, cover, hardware kit       |

**Packaging Detail**

|                       |             |
|-----------------------|-------------|
| UPC                   | 07498365546 |
| Std. Pkg. Qty.        | 1           |
| Std. Pkg. Volume (cf) | 0.5556      |
| Std. Ctn. Qty.        | 0           |
| Std. Ctn. Volume (cf) | 0.0000      |