




Part Number : [1510420002](#)

Product Description : 1.27mm Signal Pitch, 0.80mm Signal Pitch, 1.27mm Power Pitch SAS-3/PCIe-3 Plug, Vertical, Surface Mount, with Blade, 7.00mm Height, 0.60mm Peg Length, 1.40mm PCB Thickness, 68 Circuits, with Cap, Embossed Tape and Reel, Lead-Free

Series Number : 151042

Status : Active

Product Category : I/O Connectors



Documents and Resources

Drawings

[1510420002_sd.pdf](#)

[1510420002-PK-PKG.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[AS-151042-0001-001.pdf](#)

[PS-151042-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	151042
Description	1.27mm Signal Pitch, 0.80mm Signal Pitch, 1.27mm Power Pitch SAS-3/PCIe-3 Plug, Vertical, Surface Mount, with Blade, 7.00mm Height, 0.60mm Peg Length, 1.40mm PCB Thickness, 68 Circuits, with Cap, Embossed Tape and Reel, Lead-Free
Application	Board-to-Board
Comments	With Cap
Component Type	Plug
Product Name	SAS-3/PCIe-3,U.2 (SFF-8639)
Type	N/A
UPC	193264428694

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Circuits Detail	Signal 53, Power 15
Circuits (Loaded)	68
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Male
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	1.281/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.40mm
Pitch - Mating Interface	0.80mm, 1.27mm
Pitch - Termination Interface	0.80mm, 1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	0.076µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	0° to +55°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	U.2 (SFF-8639) Receptacles, SFF-8482 and SFF-8680 Receptacles, SAS / SATA Receptacles

This document was generated on Apr 27, 2026