



CONNECTORS

RUGGEDIZED BACKSHELLS & ADAPTERS



✓ Active

TE CONNECTIVITY (TE)

STXR40AC00-1418BI

Raychem

STXR40AC00-1418BI

TE Internal Number: EG3506-000

EU RoHS Compliant

Not Yet Reviewed for EU ELV

Cable Diameter Range 12.7 – 20.5 mm [.5 – .1 in]

Connector General Specification Number MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W

Connector Detail Specification Number D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47

Material Aluminum

Adapter Plating Material Electroless Nickel (AMS-C-26074)

 **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Tinel - Lock Adapter STXR Series Code 40

PDF

English

Catalog Pages/Data Sheets

5-1654025-5_sec6_Adapters

PDF

English

Product Specifications

Product Specification

Adapter Finish Specifications

PDF

English

General Information Package For Tinel-Lock Adapters

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Adapter Angle 00

Style Tinel-Lock Adapter

Termination Device Type Side-Entry Tinel-Lock Ring, Tinel-Lock Ring

Connector Shell Size 15, D

Termination Device Included TR18BI

Accessory Type Tinel-Lock Adapter

Body Features

Color Bright

Material Aluminum

Adapter Plating Material Electroless Nickel (AMS-C-26074)

TE Adapter Code 40

Adapter Entry Size 18

Termination Features

Overbraid Termination Tinel-Lock Ring

Dimensions

Cable Diameter Range 12.7 – 20.5 mm [.5 – .1 in]

Cable Entry Diameter .2 – 28.6 mm [.01 – 1.13 in]

Usage Conditions

Operating Temperature Range -65 – 200 °C [-85 – 392 °F]

Salt Spray Resistance (Hr) 48

Industry Standards

Connector Detail Specification Number D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47

Other

Connector General Specification Number MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
