


## CUSTOMER DRAWING




SCREW	PLATING SPEC
1 WITHOUT SCREWS	1 0.76um Au
2 WITH SCREWS	2 0.38um Au
	3 GOLD FLASH
	4 0.76GXT
	5 0.38GXT

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE		Amphenol	
U.S. METRIC		DRAWN	Johnny	Sep.25,2019			
.X +/- 0.25		CHECKED	Ly.Yi	Sep.25,2019		TITLE	
.XX +/- 0.20		APPROVED					
.XXX +/- 0.15		DRAWING FILE :		MINI COOL EDGE 168P STRADDLE MOUNT MATE 3.00PCB 0.00 OFFSET			
FRACTIONS +/-							
ANGLES +/- 5°		INTERNAL\ME\C ME101681340X41X		SIZE DRAWING NO. REV. A3C ME101681340X41X 5			
FOR MATERIALS AND FINISHES SEE NOTES							
REMOVE SHARP EDGES		ANGLE OF PROJECTION		SCALE		NONE	
DIMENSIONS							
—U.S.—				SHEET 1 OF 4			
INCHES							
(METRIC)							
(mm)							



This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

CUSTOMER DRAWING

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
		SEE SHEET 1		




NOTE: POSITION A1 ON OPPOSITE SIDE OF CARD OF B1  
RECOMMENDED MATING CARD



NOTE: POSITION A1 ON THE OPPOSITE SIDE OF CARD OF B1  
168PIN STRADDLE MOUNT FOOTPRINT




UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE	Amphenol	
.X	+/-	0.25		TITLE	
.XX	+/-	0.20			
.XXX	+/-	0.15		MINI COOL EDGE 168P STRADDLE MOUNT MATE 3.00PCB 0.00 OFFSET	
FRACTIONS	+/-				
ANGLES	+/-	5°		SIZE	
FOR MATERIALS AND FINISHES SEE NOTES					
REMOVE SHARP EDGES				DRAWING NO.	
DIMENSIONS					
—U.S.—	INCHES			A3 C ME101681340X41X	
(METRIC)	(mm)				
				SCALE	
				SHEET 2 OF 4	



SCREW

- NOTE:
- 1. MATERIAL: SUS304
  - 2. DIMENSIONS CONFORM TO GB823, GB93,
  - 3. THE TORQUE 0.17N.M MAX



UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE		Amphenol	
TOLERANCES		DRAWN	Johnny	Sep.25,2019			
U.S. METRIC		CHECKED	Ly.Yi	Sep.25,2019			
		APPROVED					
.X +/- 0.25				TITLE			
.XX +/- 0.20							
.XXX +/- 0.15							
FRACTIONS +/-							
ANGLES +/- 5°							
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :					
		INTERNAL\ME\C ME101681340X41X				MINI COOL EDGE 168P STRADDLE MOUNT MATE 3.00PCB 0.00 OFFSET	
REMOVE SHARP EDGES		ANGLE OF PROJECTION					
							
DIMENSIONS				SIZE		DRAWING NO.	
—U.S.—				A3		C ME101681340X41X	
INCHES						REV. 5	
(METRIC)				SCALE		NONE	
(mm)						SHEET 3 OF 4	

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

CUSTOMER DRAWING

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
		SEE SHEET 1		

