



Part Number : [192070001](#)  
Product Description : VersaKrimp Parallel  
Splice for 22-18 AWG Wire  
Series Number : 19207  
Status : Active  
Product Category : Splices  
Engineering Number : AS-302




Documents & Resources

Drawings  
[192070001\\_sd.pdf](#)

Specifications  
[PS-19902-011-001.pdf](#)  
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Splices
Series	19207
Description	VersaKrimp Parallel Splice for 22-18 AWG Wire
Product Name	Parallel,VersaKrimp
UPC	800755061239

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.766/g
Packaging Type	Bag
Wire Size (AWG)	18, 20, 22

---

### Application Tooling

#### Global

Description	Part Number
-------------	-------------

PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

---

This document was generated on Feb 07, 2025