




Part Number : [1731120859](#)
Product Description : FCT High Power Contact,
Male, Straight, Solder Cup, 0.80µm Gold
Mating Plating, 0.20µm Gold Termination
Plating, 10.0A, 20-16 AWG
Series Number : 173112
Status : Active
Product Category : D-Sub Contacts
Engineering Number : FMP027P103




Documents & Resources

Drawings
[1731120859_sd.pdf](#)

Specifications
[1731120008-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Male, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, 10.0A, 20-16 AWG
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	191128907705

Electrical

Current - Maximum per Contact	10.0A
-------------------------------	-------

Physical

Gender	Male
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	1.900/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	0.800µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +155°C

Termination Style	Solder Cup
Wire Size (AWG)	16, 18, 20

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>

This document was generated on Mar 13, 2025