

97 HZ35

Tools and harnessing machines



Manual tongs for termination of RAST 2.5 connectors in insulation displacement technology (IDT)

97

HZ35

Range of application

Connector	351..., 351...-2, 351...-4, 3520, 3521, 3522, 3523, 352...-2
Pole number	2-10 (with pitch 2.5 mm)
Pitch	2,5/5,0 mm
State of delivery of connectors	in chain, to be detached before use of the manual tongs
Processable conductor	discrete conductor, notched flat cable 2.5/5.0 mm

Features

Application	laboratory and sample production, harness repair
Stroke capacity	ca. 240/h
Scope of functions and delivery	- Harnessing of bus cables possible - In transport case - The handle color may vary during a period of transition.
Options	- Special press die, required for 351... with side P1 being closed - Special press die, required for 3517-5 (for 1 mm printed circuit board)

Dimensions and supply data

Dimensions (H x W x D)	50 mm x 60 mm x 240 mm
Weight	ca. 1 kg

97

HZ35

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
HZ35	-		