



Image coming soon

Part Number : [1301040054](#)
Product Description : Guard Assembly for 61430
Incandescent Hand Lamp
Series Number : 130104
Status : Active
Product Category : Portable Lighting Accessories
Engineering Part Number : 61431

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Portable Lighting Accessories
Series	130104
Description	Guard Assembly for 61430 Incandescent Hand Lamp
NEMA Configuration	N/A
Product Name	Woodhead
Type	Accessory
UPC	78678861431

Agency

CSA	LR39801
-----	---------

Electrical

Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Cast Aluminum
Height	N/A
Lamp Type	N/A
Length	N/A
Material - Globe	Tempered Soda-Lime Glass

Material - Guard	Cast Aluminum
Net Weight	2969.585/g
Outlet	None
Packaging Type	Carton

This document was generated on Jan 04, 2026