

**Part Number :** [1300970197](#)

**Product Description :** Deluxe Cord Grips Strain Relief, 1/2" NPT, 45° Angle Male, Cable Diameter 4.75-6.35mm (.187-.250")

**Series Number :** 130097

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 36310



---

## Documents and Resources

### Drawings

[1300970197 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130097
Description	Deluxe Cord Grips Strain Relief, 1/2" NPT, 45° Angle Male, Cable Diameter 4.75-6.35mm (.187-.250")
Hazardous Locations	Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
NEMA Rating	NEMA 4
Product Name	Deluxe Cord
Type	Strain Relief Grip
UPC	78678836310

### Agency

CSA	LR32159
UL	E76954

### Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	45° Angle
Cable Diameter	4.75-6.35mm (.187-.250")
Color - Grommet	Orange
Eye Type	N/A
Gender	Male
Material - Body	Aluminum
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	N/A
O-Ring	N/A
Thread Size	1/2" NPT

## Mates With / Use With

### Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	<u>1300990149</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

---

This document was generated on Dec 07, 2025