



# YA26L2TC3890

by Burndy  
Catalog ID: YA26L2TC3890

Prop 65 Notice

COPPER COMPRESSION TERMINAL.

## Product Details

### General

|                                      |                                                                              |
|--------------------------------------|------------------------------------------------------------------------------|
| Color Code                           | Black                                                                        |
| Connector Type                       | Terminal                                                                     |
| Die Index                            | 13                                                                           |
| Feature - Barrel Style               | <ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul> |
| Feature - Barrel Type                | Standard                                                                     |
| Material                             | Copper                                                                       |
| Physical Attribute - Number of Holes | 2                                                                            |
| Physical Attribute - Tongue Type     | Standard                                                                     |
| Plated                               | Y                                                                            |
| Plating Type                         | Tin - Electro Plated                                                         |
| Trade Name                           | HYLUG™                                                                       |
| Type                                 | Standard Barrel, Tin Plated                                                  |
| UPC                                  | 781810019399                                                                 |
| UPC 12 Digit                         | 7818100193999                                                                |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - B Length fraction     | 15/16 in |
| Dimension - B Length inch         | 0.94 in  |
| Dimension - Bolt Hole Size inch   | 0.39 in  |
| Dimension - Bolt Size fraction    | 3/8      |
| Dimension - D inch                | 1.83 in  |
| Dimension - Hole Size inch        | 0.40 in  |
| Dimension - Hole Size mm          | 10 mm    |
| Dimension - L Length Overall mm   | 56 mm    |
| Dimension - Length Overall inch   | 2.22 in  |
| Dimension - N inch                | 0.41 in  |
| Dimension - Outside Diameter inch | 0.56 in  |
| Dimension - Pad Width inch        | 0.83 in  |
| Dimension - Strip Length inch     | 1 in     |
| Dimension - Stud Size inch        | 3/8      |

|                                   |           |
|-----------------------------------|-----------|
| Dimension - Z inch                | 0.42 in   |
| Physical Attribute - Tongue Angle | 90 Degree |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

### Conductor Related

|                                        |               |
|----------------------------------------|---------------|
| Conductor - Copper Str Navy Size       | 125 (61) Navy |
| Conductor - Copper Str Navy Size Range | 125 (61) Navy |
| Conductor - Copper Str Size            | 2/0 AWG       |
| Conductor - Copper Str Size Range      | 2/0 AWG       |
| Conductor - Material                   | Copper        |

### Certifications and Compliance

|                                    |              |
|------------------------------------|--------------|
| Certification - CSA Approved       | Yes          |
| Certification - ETL                | No           |
| Certification - UL Recognized      | No           |
| Certification - cULus              | No           |
| Industry Standard(s)               | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM           |
| UL Listed                          | Yes          |

### Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

For further technical assistance, please contact us

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
       1-603-647-5299 (International)