T1010, Uninsulated Ring Terminal, 12-10 AWG, #8-10 Stud



By Burndy
Catalog # T1010

Uninsulated Ring Terminal For 12 - 10 AWG, #8-10 Stud, Tin Plated, Brazed Seam

Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21
Width	13 in
Dimension - Hole Size inch	0.2 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8 - #10
Dimension - Bolt Size fraction	#8 - #10
Dimension - B Length fraction	17/50 in
Dimension - Z inch	0.29 in
Dimension - B Length inch	0.34 in
Depth	15 in
Height	11 in
Dimension - Diameter Max Size inch	0.12 in
Dimension - Length Overall inch	0.82

General

Product Family	COMPRESSION
Trade Name	HYLUG™
Feature - Barrel Type	Standard
Plated	Yes
Physical Attribute - Tongue Type	Ring
Sub Brand	HYLUG
Product Type	Terminal
Listings	UL, CSA
UPC	781810722084
Type	Ring Tongue
Material	Carbon Steel
Plating Type	Tin
UPC 12 Digit	781810722084
UPC 14 Digit GTIN	00781810722084

Logistics

Minimum Pack Quantity	50
Pallet Quantity	99999
Carton Quantity	600

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.