Part Number : 2204240004
Product Description : Squba Weather Cap for 4 or 2 Circuit Receptacle Housing
Series Number : 220424
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

2204240004_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2042200000-AS-000.pdf

2077760000-AS-000.pdf

2042200000-PS-000.pdf

2042200000-TS-000.pdf

2077760000-PS-000.pdf

2077760000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	220424
Description	Squba Weather Cap for 4 or 2 Circuit Receptacle Housing
Component Type	Cap
Keyword	Squba 1.8
Product Name	Squba
UPC	196823073762

Physical

Circuits (Loaded)	2, 4
Circuits (maximum)	2, 4
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	0.890/g
Packaging Type	Bag

Downloaded from Arrow.com.

Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Squba 1.8 Sealed Single Row Receptacle Assemblies	204220
Squba 3.6 Sealed Single Row Receptacle Assemblies	207782

Downloaded from Arrow.com.